



Coil Spring Separator **BANE PET** CSS SERIES



Put the entangled coil spring into "BANE PET".

The "BANE PET" Coil Spring Separator save time and boosts productivity

Coil springs are usually supplied by manufacturers to their users with a carton or bag packing, in which springs are entangled each other. Entangled springs are to be separated when used by hand, but such a manual work causes various troubles such as time-consuming, changing shapes, etc. In order to solve these problems, BANE PET has been developed. By using springs separated by BANE PET, much faster works could be possible, and the products themselves can be manufactured keeping a high quality standard.



The entangled coil spring is automatically unraveled.

Features

■ Easy Installation

Because the "BANE PET" uses a conventional power source, it can be placed anywhere within reach of a standard wall receptacle. This means easier access to equipment and greater flexibility in its placement.

■ Compact and Portable

The "BANE PET" is so compact and lightweight that anyone can handle it with ease. Portability of this kind promotes greater productivity.

■ Quiet Operation

We've paid special heed to the user's environment for the same reason...it boosts productivity. Thus the "BANE PET" is designed to provide quiet, noise-free operation.

■ Spring Size Adjustment

This convenient feature lets you run one size coil, and switch to another in moments. Operation couldn't be simpler.

■ Versatile Application

The "BANE PET" is equipped to separate both tapered and hooked coil springs, depending on the task at hand. It can untangle coils with sizes ranging from 2mm to 10mm in diameter, and is ideal for use in assembly lines, repair shops, and at home.


FUJI CONTROLS CO., LTD.

Coil Spring Separator

CSS SERIES

BANE PET

Dimensional drawing



* Since this is a resin molded product, there are variations in dimensions.

Specification

Model:CSS-S4		
Applicable spring size		
Outside coil diameter	Dmm	ϕ 2~10
Free length	Lmm	L2~20
Wire diaments	dmm	ϕ 0.2~0.4
Power requirements		AC100-240V 50/60Hz
Power consumption		10VA
Dimensional drawing		230 × 120 × 190mm
Weight (approx)		1kg
Accessory		Separated spring Receptacle (175×255mm)

Notes

When enquiring, please specify the kind and material of the coil springs you use. The "BANE PET" may not be applicable for certain types of coil springs.
When ordering, please specify your voltage requirement.

The "BANE PET" is equipped with a 2-prong power plug; use an adapter where necessary.

Other models are available for springs having a coil diameter less than or greater than 2mm to 10mm.

Write to us about your requirement.

The standard kit is set for springs coiled clockwise, so that if springs coiled anticlockwise are worked out, you are requested to inquire so.

FOR FURTHER DETAILS, WRITE TO OUR SALES DEPARTMENT.

* Product specifications are subject to change for improvement. Please note.

* Product color may differ from the actual product due to printing.

* Be sure to read the instruction manual for necessary information such as precautions for use.

FUJI CONTROLS CO., LTD.

1-5-6 IIDABASHI, CHIYODA-KU TOKYO 102-0072 JAPAN

TEL : 03-3265-5437

FAX : 03-3265-5430

E-mail : sales@fujicon.net

web site

<https://www.fujicon.net>